



## Recessed 6" Series, Cover Assembly, Satin Nickel Plated Finish

By Hubbell Premise Wiring  
Catalog # [S1R6CVRNKL](#)

Fire Rated Poke Throughs, Recessed 6" Series, Cover Assembly, Satin Nickel Plated Finish



### Features

- 180 Degree Cover Opening to Lay Flat and Reduce Tripping Hazards
- Two Large Cable Egress Doors
- Die Cast Aluminum Cover Construction for Enhanced Durability
- ADA Compliant

### Application

6" Fire-Rated Poke-Through Series

### General

Accessory Type	6" Round Recessed Cover
Application - For Use On	Concrete
Color	Nickel
EU RoHS Indicator	Contact Manufacturer
Finish Type	Satin Nickel Plated Cover
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Aluminum
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	Screw Mount
Size	Standard Sized Product
Style	Covers
Sub Brand	SystemOne Recessed
Type	6" Recessed Fire Rated Poke Through Covers
UPC	783585443461

### Conductor Related

Cable Entry Through Cover

### Certifications and Compliance

- Industry Standard(s)
- cULus Listed
  - Meets ADA Standards
  - UL 514A Listed

### Product Assets

[Catalog Page - PREM R38 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)

### Related Products

[S1R6PTFITCHI - Recessed 6" Series, Through Floor Fitting Only, No Sub Plates, No Junction Box](#)  
[S1R6PTFIT - Recessed 6" Series, Through Floor Fitting With \(1\) S1FRPT Hubbell Junction Box Only, No Sub Plates](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-S1R6CVRNKL-SPEC-EN | REV 7/2023