

HUBBELL Premise Wiring

Recessed 6" Series, Kit

By Hubbell Premise Wiring
Catalog # [S1R6PTDEHBRS](#)

Fire Rated Poke Throughs, Recessed 6" Series, Kit, (1) S1R6PTFIT, (1) S1R6SPD, (1) S1R6SPE, (1) S1R6SPH, (1) S1R6CVRBRS



Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

General

Accessory Type	6" FRPT Kit
Application	6" Fire-Rated Poke-Through Series
Application - For Use On	Concrete
Catalog Number	S1R6PTDEHBRS
Color	Brass
EU RoHS Indicator	Contact Manufacturer
Finish Type	Brushed Brass Plated Cover
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	6" Core Hole
Number Of Outlets	(2) 50% Left Side Sub Plates- (3) iSTATION Opening, (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings and (1) 50% Right Side- (4) 20A Pre-Wired Receptacles, 1 or 2 Circuits, 18" Leads
Size	Standard Sized Product
Style	FRPT - Complete Kits
Sub Brand	SystemOne Recessed
Type	6" Recessed Rated Poke Through Kit
UPC	783585443249

Conductor Related

Cable Entry	Through Cover
-------------	---------------

Certifications And Compliance

Industry Standard(s)	cULus Listed
	Meets ADA Standards
	UL 514A Listed

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog Page - WDK P-17](#) [Catalog Page - PREM T42](#) [Catalog Page - WDK Catalog Full 2024](#) [Catalogs - Premise Wiring Catalog](#) [Customer Notices - Prop 65 Notice](#) [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
PREM-SIR6PTDEHBRS-SPEC-EN | REV 6/2024