

Recessed 6" Series, Kit

By Hubbell Premise Wiring
Catalog # [S1R6PTDEHGRY](#)

Recessed 6" Series, Kit, (1) S1R6PTFIT fitting; (1) S1R6CVRGRY Gray Painted Recessed Cover; (1) S1R6SPD Sub Plate; (1) S1R6SPE Sub Plate; (1) S1R6SPH Sub Plate; (1) S1R6DIV Low Voltage Divider and (1) S1FRPT Hubbell Junction Box

Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

6" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s)	• cULus Listed • Meets ADA Standards • UL 514A Listed
----------------------	---

Conductor

Cable Entry	Through Cover
-------------	---------------

Configuration

Number Of Outlets	(2) 50% Left Side Sub Plates- (3) iSTATION Opening, (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings and (1) 50% Right Side- (4) 20A Pre-Wired Receptacles, 1 or 2 Circuits, 18" Leads
-------------------	--

Dimensions



Size	Standard Sized Product
General	
Application - For Use On	Concrete
Color	Gray
Style	FRPT - Complete Kits
Mounting Type	6" Core Hole
UPC	783585590042
Accessory Type	6" FRPT Kit
Type	6" Recessed Rated Poke Through Kit
Material - Mounting Hardware	Mounting Hardware Included
Construction	Fabricated
Construction Material - Main Item Type	6 Meunt 6" Recessed Fire-Rated Poke-Through Components
Sub Brand	SystemOne Recessed
Material	Fabricated
Finish Type	Gray Powder Coat Cover
Logistics	
Carton Quantity	1
Product Assets	
Catalog [English]	
Catalog [English]	
Catalog Page [English]	