

Recessed 6" Series, Through Floor  
Fitting Only, No Sub Plates, No  
Junction Box

By Hubbell Premise Wiring  
Catalog # [S1R6PTFITCHI](#)

Fire Rated Poke Throughs, Recessed 6" Series, Through Floor  
Fitting Only, No Sub Plates, No Junction Box

Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

6" Fire-Rated Poke-Through Series

General

Accessory Type	6" FRPT
Application - For Use On	Concrete
Catalog Number	S1R6PTFITCHI
Color	Metallic
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Mounting Type	6" Core Hole
Size	Standard Sized Product
Specifications	<ul style="list-style-type: none"><li>• Fire Resistance Rating - 2-Hrs. (D900)</li><li>• Floor thickness - 2 1/4 in. (57.2)</li></ul>



Style  
Sub Brand  
Type

UPC

- Max. Cu Cross Section - 3/4 in. Power EMT .0307 sq. in.
  - Mounting - 6 in. (152.4)
- FRPT Kits  
SystemOne Recessed  
6" Recessed Rated Poke  
Through Only  
783585443195

Conductor Related

Cable Entry Through Cover

Certifications And Compliance

Industry Standard(s) cULus Listed

Logistics

Carton Quantity 1

Product Assets

[Catalog Page - PREM T37 Catalog Page](#)  
[Catalog Page - WDK P-18 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)  
[Specifications - S1R6PTFITCHI](#)