

HUBBELL

Premise Wiring

Recessed 6" Series, Sub Plate, 50% Right Side, (3) 20A Pre-Wired Tamper Resistant Receptacles, 1 Circuit, 18" Leads

By Hubbell Premise Wiring
Catalog # [S1R6SP3RTR](#)

Recessed 6" Series, Sub Plate, 50% Right Side, (3) 20A Pre-Wired
Tamper Resistant Receptacles, 1 Circuit, 18" Leads

Features

- Steel Construction
- White Powder Coat Paint
- Includes IG and CONTROLLED Stickers and Necessary Mounting Hardware

Application

6" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s) cULus Listed

Conductor

Cable Entry Through Cover

Configuration

Number Of Outlets (3) 20A Pre-Wired Tamper
Resistant Receptacles, 1 Circuit,
18" Leads

General



Application - For Use On	Concrete
Color	White
Style	Sub-Plates
Mounting Type	Screw Mount
UPC	783585696485
Accessory Type	Sub Plate
Type	6" Recessed Rated Poke Through Sub Plates
Material - Mounting Hardware	Mounting Hardware Included
Construction	Fabricated
Item Type	6" Recessed Fire-Rated Poke- Through Components
Sub Brand	SystemOne Recessed
Material	Fabricated
Finish Type	White Paint

Logistics

Carton Quantity 12

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English, Spanish, French\]](#)