

HUBBELL
Premise Wiring

Recessed 8" Series, Sub Plate, Perimeter, (2)
20A Pre-Wired Tamper Resistant
Receptacles, 1 Circuit, 18" Leads

By Hubbell Premise Wiring
Catalog # [S1R8PSPZTR](#)

Recessed 8" Series, Sub Plate, Perimeter, (2) 20A Pre-Wired Tamper
Resistant Receptacles, 1 Circuit, 18" Leads

Features

- Steel Construction
- White Powder Coat Paint
- Includes IG and CONTROLLED Stickers and Necessary Mounting Hardware

Application

8" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s) cULus Listed

Conductor

Cable Entry Through Cover

Configuration

Number Of Outlets (2) 20A Pre-Wired Tamper
Resistant Receptacles, 1 Circuit,
18" Leads

General



Application - For Use On	Concrete
Color	White
Style	Sub-Plates
Mounting Type	Screw Mount
UPC	783585696461
Accessory Type	Perimeter Sub Plate
Type	8" Recessed Rated Poke Through Sub Plates
Material - Mounting Hardware	Mounting Hardware Included
Construction	Fabricated
Item Type	10" Recessed Fire-Rated Poke- Through Components
Sub Brand	SystemOne Recessed
Material	Fabricated
Finish Type	White Paint

Logistics

Carton Quantity 20

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English, French, Spanish\]](#)