



**Recessed 8" Series, Through Floor Fitting Only, (1) S1R8JNC2 fitting box, No S1FRPTJB, No Flexible Metal Conduit, No Sub Plates**

By Hubbell Premise Wiring  
Catalog # [S1R8PTFIT2CHI](#)

Fire Rated Poke Throughs, Recessed 8" Series, Through Floor Fitting Only, (1) S1R8JNC2, No S1FRPTJB, No Flexible Metal Conduit, No Sub Plates

**Features**

- For use with a 8.00" to 8.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

**Application**

8" Fire-Rated Poke-Through Series

**General**

Accessory Type	8" FRPT Kit
Application - For Use On	Concrete
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Item Type	8" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Mounting Type	8" Core Hole
Performance	<ul style="list-style-type: none"><li>• Mechanical - Mounting - In 8"(203.2) cored concrete diameter through hole</li><li>• Mechanical - Wire - Three #12 AWG solid conductors</li></ul>
Size	Standard Sized Product
Style	FRPT Fittings
Sub Brand	SystemOne Recessed
Type	8" Recessed Rated Poke Through Kit
UPC	783585443911



**Conductor Related**

Cable Entry Through Cover

**Certifications And Compliance**

- |                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• cULus Listed</li><li>• UL 514A Listed</li></ul> |
|----------------------|---|

**Product Assets**

[Catalog Page - WDK P-14](#) [Catalog Page - PREM T35](#) [CatalogPage Catalogs - Premise Wiring Catalog](#) [Catalogs - WDK Catalog Full 2024](#) [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)



A proud member of the Hubbell Family.