



Recessed 8" Series, Kit

By Hubbell Premise Wiring
Catalog # [S1R8PTZZ2BLK](#)

Fire Rated Poke Throughs, Recessed 8" Series, Kit, (1) S1R8PTFIT1, (2) S1R8SPZ, (1) S1R8JNC2, (1) S1R8CVRBLK



Features

- For use with a 8.00" to 8.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

8" Fire-Rated Poke-Through Series

General

Accessory Type	8" FRPT Kit
Application - For Use On	Concrete
Color	Black
EU RoHS Indicator	Contact Manufacturer
Finish Type	Black Powder Coat Cover
Item Type	8" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	8" Core Hole
Number Of Outlets	(2) Two 20A Pre-Wired Receptacles, 1 or 2 Circuits, 18" Leads
Size	Standard Sized Product
Style	FRPT - Complete Kits
Sub Brand	SystemOne Recessed
Type	8" Recessed Rated Poke Through Kit
UPC	783585443980

Conductor Related

Cable Entry Through Cover

Certifications and Compliance

- Industry Standard(s)
- cULus Listed
 - Meets ADA Standards
 - UL 514A Listed

Product Assets

[Catalog Page - PREM R41 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)

Related Products

[S1R8CSPJ - Recessed 8" Series, Sub Plate, Center, Single Gang, \(1\) 1.40" Opening](#)
[S1R8CSPK - Recessed 8" Series, Sub Plate, Center, Single Gang, \(1\) Style Line® Decorator Opening](#)
[S1R8CSPEXT - Recessed 8" Series, Sub Plate, Center, Two Gang, 1" Extender, 3rd Party Data Device](#)
[S1R8CSPE - Recessed 8" Series, Sub Plate, Center, Single Gang, \(1\) 1.5-Unit iSTATION Opening](#)
[S1R8CSPG - Recessed 8" Series, Sub Plate, Center, Single Gang, \(1\) 1.60" Opening](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-S1R8PTZZ2BLK-SPEC-EN | REV 7/2023