



Hubbell Premise Wiring

Stereo Jack, 3.5 MM Stereo Jack, Female, 110 Block Terminations, Black

By Hubbell Premise Wiring
Catalog # [SF35110BK](#)



Stereo Jack, 3.5 MM Stereo Jack, Female, 110 Block Terminations, Black

General

Contact	Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Snap-Fit Data and AV Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
OEM Brand Name	Hubbell Premise Wiring
Temperature Rating	Per TIA
Type	RCA
UPC	662620306902

Dimensions

Display Size	1-Unit
--------------	--------

Electrical Ratings

Connectivity	110 Punch Down Block
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Literature - iSTATION 110 Termination 3.5mm Stereo Jack](#)
- [Literature - Hubbell AV 110 Everywhere™](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - Integrating AV Systems](#)
- [Literature - iSTATION Keystone VGA Screw Terminal Connector](#)
- [Sales Drawings - SF35110BK - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-SF35110BK-SPEC-EN | REV 7/2023