




Hubbell Premise Wiring

Snap-Fit, F-Coax Connector, Electric Ivory

By Hubbell Premise Wiring
Catalog # [SFFEX](#)



Snap-Fit, F-Coax Connector, Electric Ivory

Application

Snap-Fit F-Connector

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and F-Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
OEM Brand Name	Hubbell Premise Wiring
Style	Nickel, 2GHz
Temperature Rating	Per TIA
Type	F-Type
UPC	662620809786

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Female to Female
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - PREM S47 Catalog Page](#)
- [Catalog Page - PREM F9 Catalog Page](#)
- [Catalogs - HPW CATALOG_2023_FULL](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
- [Literature - Integrating AV Systems](#)
- [Sales Drawings - SFF - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-SFFEX-SPEC-EN | REV 7/2023