



## Snap-Fit, Recessed F-Coax Connector, Black

By Hubbell Premise Wiring  
Catalog # [SFGRFBK](#)



Snap-Fit, Recessed F-Coax Connector, Black

### Application

Snap-Fit Gold F-Connector, Recessed

### General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION RCA and F-Keystone Connectors
Material - Mounting Hardware	Snap-On- Snap-Fit
OEM Brand Name	Hubbell Premise Wiring
Style	Gold, Recessed
Temperature Rating	Per TIA
Type	F-Type
UPC	662620202389

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Connectivity	Female to Female
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)  
[Literature - Healthcare Application Guide](#)  
[Literature - Integrating AV Systems](#)  
[Sales Drawings - SFGRF - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-SFGRFBK-SPEC-EN | REV 7/2023