



Wallplates and Boxes, Metallic Plates, 2- Gang, 2) GFCI Openings, Standard Size, Stainless Steel

By Hubbell Premise Wiring
Catalog # [SS262](#)

Wallplates and Boxes, Metallic Plates, 2- Gang, 2) GFCI Openings, Standard Size, Stainless Steel



Features

- Environments subjected to heavy abuse
- Ideal for highly corrosive environments
- Magnetic: 17.0% Chromium, Less than 0.5% Nickel
- Finish is lacquer coated to inhibit oxidation

Application

Protection against contact of live terminals and wiring.
Provides finished look to installation.

General

Construction	Stamped
Cutout	2) Decorator
EU RoHS Indicator	Yes
Item Type	Decorator Wallplates
Material	Stainless Steel
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	2-Gang
Type	<ul style="list-style-type: none">• Plates• Plates
UPC	883778201677

Dimensions

Display Size	Standard Sized
Thickness	0.04
Weight	0.1 lb

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - PREM B9 Catalog Page](#)
[Catalog Page - Wiring AA-12 Catalog Page](#)
[Catalog Page - PREM T7 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-SS262-SPEC-EN | REV 7/2023