

HUBBELL

Premise Wiring

Copper Solutions, Patch Cord, AV, 8-Pin and 3.5 MM Stereo Jack, Plenum Rated, 5' Length, Black

By Hubbell Premise Wiring
Catalog # [VGA36P05BK](#)



Copper Solutions, Patch Cord, AV, 8-Pin and 3.5 MM Stereo Jack, Plenum Rated, 5' Length, Black

General

Boot Type	None
Catalog Number	VGA36P05BK
EU RoHS Indicator	Yes
Item Type	X-END AV Plug-n-Play System
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Plug Type	VGA
Temperature Rating	Per TIA
Type	VGA, Plug-n-Play
UPC	662620242620

Dimensions

Outside Diameter	0.375
------------------	-------

Electrical Ratings

Voltage Rating	600V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#28 AWG

Logistics

Carton Quantity	75
-----------------	----

Product Assets