



XLR Connector, Solder Type, Panel Mount, 3-Pin, 10 Pack

By Hubbell Premise Wiring
Catalog # [XLR10](#)

XLR Connector, Solder Type, Panel Mount, 3-Pin, 10 Pack



Application

D-Style XLR 3-Pole Locking Connection

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION Pro Audio D-Style Connections
Material - Mounting Hardware	Snap-On- Snap-Fit
OEM Brand Name	Hubbell Premise Wiring
Temperature Rating	Per TIA
Type	XLR
UPC	662620285412

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Solder
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity 5

Product Assets

[Literature - Integrating AV Systems](#)
[Sales Drawings - XLR10 - PDF](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-XLR10-SPEC-EN | REV 7/2023