

**Cable**  
**UTP Cables**  
**NEXTPOWER CATEGORY 5E 4PPoE**

# HUBBELL

**Features**

- 100W OF POWER AND 1 GIGABIT ETHERNET PERFORMANCE
- TESTED 350 MHz
- PoE and PoE+ Ready
- CABLE-ID ALPHA NUMERIC CODE PRINTED
- Guaranteed 0.3 dB headroom for IL, ACR and PSACR

**Ordering Information**

Description	Color	Catalog Number	UPC Number
NEXTPOWER CATEGORY 5E 4PPoE, 4-PAIR, UTP CABLE	ORANGE	C5ELPPOR	662620660059

**Listings**

ANSI/TIA-568-C.2 (CATEGORY 5E 4PPoE)  
 UL LISTED  
 UL VERIFIED  
 IEEE 802.3af (PoE), IEEE 802.3at (PoE+), IEEE 802.3bt (4PPPoE)

**Specifications**

Wire	22 AWG SOLID ANNEALED COPPER
Primary Insulation	CMP:FEP
Primary Insulation	CMR Polyolefin
Cabling	4 Unshielded Twisted Pairs
Outer Jacket	Flame Retardant,Low Smoke PVC

**Performance**

Installation Temperature	(-0C to +60C (32F to +140F))
Operation Temperature	(-20C to +75C (-4F to +167F))

**Applications**

4PPoE – IEEE 802.3bt Type 3 and 4 draft D1.2  
 HDBaseT Class A and B  
 PoE Applications

**Accessories**

SPEEDGAIN Jacks, Category 5e	<b>HXJ5E Series</b>
SPEEDGAIN Patch Panel, Category 5e	<b>HP5Exx (xx=Ports)</b>
SPEEDGAIN Patch Cords, Category 5E	<b>HC5Exxyy (xx = color, yy = length in feet)</b>

