

Cable
UTP Cables
NextPower Catrgory 5E 4PPoE

HUBBELL

Features

- 100W of Power and 1 Gigabit Ethernet Performance
- Tested 350 MHz
- PoE and PoE+ Ready
- Cable-id Alpha Numeric Code Printed
- Guaranteed 0.3 dB headroom for IL, ACR and PSACR

Ordering Information

Description	Color	Catalog Number	UPC Number
NextPower Category 5E 4PPoE, 4-Pair, UTP Cable	Violet	C5ELPRV	662620619682



Listings

ANSI/TIA-568-C.2 (CATEGORY 5E 4PPoE)
UL Listed
UL Verified
IEEE 802.3af (PoE), IEEE 802.3at (PoE+), IEEE 802.3bt (4PPPoE)

Specifications

Wire	22 AWG Solid Annealed Copper
Primary Insulation	CMP:FEP
Primary Insulation	CMR Polyolefin
Cabling	4 Unshielded Twisted Pairs
Outer Jacket	Flame Retardant PVC

Performance

Installation Temperature	(-40C to +75C (-40F to +167F))
Operation Temperature	(-20C to +75C (-4F to +167F))

Applications

4PPoE – IEEE 802.3bt Type 3 and 4 draft D1.2
HDBaseT Class A and B
PoE Applications

Accessories

SPEEDGAIN Jacks, Category 5e	HXJ5E Series
SPEEDGAIN Patch Panel, Category 5e	HP5Exx (xx=Ports)
SPEEDGAIN Patch Cords, Category 5E	HC5Exxyy (xx = color, yy = length in feet)