

Floor Boxes

SystemOne ETERNAL™ Series Concrete Floorboxes 4/5-Gang Recessed

HUBBELL

Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- External High Capacity Feed-Thru Hubs Sold Separately
- Stamped steel construction, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

Ordering Information

Cover Style	Box Type	Catalog Number	UPC Number
Round	Above Grade	CFB45G55RE	783585695419



Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	16 gauge galvanized steel
Box Finish	Natural
Top Mousing Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(2) Small 35 IN ³ [574 CM ³], (2) Med 69.5 IN ³ [1139 CM ³], (2) Large 99 IN ³ [1622 CM ³]

Performance

Height

6.31" [160.2mm]

Length

14.14" [359.2mm]

Trade Size Knock-Outs: Ends

(2) 3/4", 1", 1 1/4", 2" (Field installed CFBHUB2 for 2" metallic conduit, CFBHUB200PVC for 2" PVC conduit or CFBHUB125PVC for 1 1/4" PVC conduit)

Width

11.09" [281.6mm]

Accessories

(2) 2" PVC field installed hubs, ships with (2) 1-1/2" reducer, (2) 1-1/4" reducers, and (2) 1" reducers/plugs	CFBHUB200PVC
(2) 1-1/4" PVC field installed hubs, ships with (2) 1" reducers, (2) 3/4" reducers, AND (2) 1/2" reducer/plugs	CFBHUB125PVC
2" threaded zinc hub	CFBHUB2
3/4" Prepour stackable ring extensions	CFB8RCVRR075
(1) SyleLine Decorater Opening	FB10MPREC

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

