

Floor Boxes

SystemOne Recessed Floorboxes

4-Gang Recessed

HUBBELL

Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- External High Capacity Feed-Thru Hubs Sold Separately
- PVC base construction for on grade use, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates



Ordering Information

Cover Style	Box Type	Catalog Number	UPC Number
Round	On/ Above Grade	CFB4G30PFBRE	783585695440

Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	PVC
Box Finish	Gray
Top Mouning Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	Green #10-32 Screw
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(4) 51.0 IN³ [835 CM³]

Performance

Height

3.88"[98.6mm]

Length

15.70" [398.8mm]

PVC Conduit Entry: Ends

Requires Drilling Openings. PVC Conduit Only: 1¼" Maximum Size *

Width

11.20" [284.5mm]

Accessories

(2) 2"PVC field installed hubs, ships with (2) 1-1/2" reducer, (2) 1-1/4" reducers, and (2) 1" reducers/plugs	CFBHUB200PVC
(2) 1-1/4" PVC field installed hubs, ships with (2) 1" reducers, (2) 3/4" reducers, AND (2) 1/2" reducer/plugs	CFBHUB125PVC
3/4" Prepour stackable ring extensions	CFB8RCVRR075

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions