

OptiChannel
Duplex Fiber Patch Cords, Riser
LC to LC, Multimode, OM1

HUBBELL

Features

- Precision Zirconia Ferrule, PC Polish
- 100% Tested, Heat Cured Epoxy Termination
- Available in Lengths 1 to 10 meters
- Custom Lengths Quoted to Order



Ordering Information

Description	Cable Type	Catalog Number	UPC
Fiber Patch Cord, Riser, Duplex, LC to LC, OM1, 5M	Duplex Zipcord, OM1, Orange	DFRCLCLCC5MM	662620328089

Standards

TIA-568.3
TIA-604-FOCIS
Telcordia GR-326-CORE
TIA-492AAAA (OM1, Legacy)
ANSI/ICEA S-83-596
TIA-598

Specifications

Overall Length	5 meters (16.41 ft)
Ferrule Material	Zirconia Ceramic
Cable Diameter	1.6 mm to 2.0 mm
Mated Pair Insertion Loss	< 0.50 dB (0.35 dB Typical)
Mated Pair Return Loss	> 26 dB
Polarity	A-B

Performance

Mechanical	
Mating Durability	500 Cycles, < 0.75dB
Minimum Bend Radius	25 mm (1.0 in.)
Operating Temperature Range	0C to 70C (32F to 158F)
Tensile Rating, Short Term	11.24 Lb (50 N)

Applications

10 Gbps/25 Gbps Fiber Channel
Backbone/Horizontal Distribution Interconnect
Data Center Equipment Interconnect

Accessories

Fiber Microscope, 200X	OFSCOPE2
Fiber Cleaning Kit	OFCLEANKT1
Fiber Wipes Dispenser, 90 Sheets	OFWIPES90
Fiber Cleaning Fluid, 3 Oz.	OFCLEANER3OZ

Online Resources

Customer Use Drawing
eCatalog

