

OptiChannel
Fiber Connector
OM2, MM

HUBBELL

Features

- Pack of 10 connectors
- Each in a protective blister pack with cleave protector, extended dust cap, 900µm boot and splice sleeve
- Compatible with fusion splicers having a removable fiber holder
- Metal holder fixture required (sold separately)
- Hubbell fusion splice heat shrink oven, Catalog Number FCSPLHSOVEN is also required for termination



Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Optic, Connector, Fusion Splice, FC, OM2, Pre-Polished, 900, Pack of 10, Blister Pack	Beige	FCFCF900M50BP	662620343594

Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Performance

Environmental	
Operating temperature	0 °C to 70 °C
Optical	
Insertion loss	0.5dB (0.35dB typical), 0.75dB max
Mating durability	500 cycles, 0.1dB change
Multimode return loss	35dB Typ, 22dB minimum
Singlemode return loss	55dB Typ, 40dB minimum

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions
Sales Drawing