

Features

- Maximum Density, 144 LC Ports in a 1U Rack Space
- Three Independent Slide-Out Drawers
- Accepts OCLCHD-Series Ultra Compact Cassettes



Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Products, Rack Mount Panel, 1U, 12 HD Casstette, 12-HD-LC,	Grey	FCRHD1UGY	662620238142

Specifications

Type	High Density Enclosures
Style	Unloaded, HD Cassette
Number Of Ports	144
Application	Ultra High Density for Data Center Applications; Complete Interconnect system for 10G, 25G, 40G, 50G, 100G, 200G , 400G and Beyond; Full Compliment of LC-MPO and MPO Cassettes
Compatibility	OCLCHD Cassettes and OCHDMTP Adapters
Material	16 gauge cold rolled steel

Dimensions- inches (mm)

Depth	17" (432mm)
Width	19" (483 mm)
Height	1.75" (44mm)

Online Resources

eCatalog