

Racks and Enclosures High Density Enclosures

HUBBELL

Features

- Maximum Density, 576 LC Ports in a 4U Rack Space
- Independent Slide-Out Drawers
- Accepts OCLCHD-Series Ultra Compact Cassettes



Ordering Information

Description	Color	Catalog Number	UPC Number
Fiber Products, Rack Mount Panel, 4-Unit, 48 HD Casstette, 48-HD-LC,	Black	FCRHD4UBK	662620612843

Specifications

Type	High Density Enclosures
Style	Unloaded, HD Cassette
Number Of Ports	576
Application	Ultra High Density for Data Center Applications; Complete Interconnect system for 10G, 25G, 40G, 50G, 100G, 200G , 400G and Beyond; Full Compliment of LC-MPO and MPO Cassettes
Compatibility	OCLCHD Cassettes and OCHDMTP Adapters
Material	16 gauge cold rolled steel

Dimensions- inches (mm)

Depth	25.7" (653mm)
Width	19" (483 mm)
Height	7.00" (178mm)

Online Resources

Customer Sales Drawings
eCatalog
Sales Drawing