

Connectors

Fiber Optic Connectors

HUBBELL

Features

- Terminate in Less than 60 Seconds
- RoHS Compliant and Bulk Packed in Recyclable Cartons



Ordering Information

Description	UPC Number	Catalog Number
Fiber Optic Connectors, ST-Single Mode, Pre-Polished, 12 Pack	662620217482	FCSTSM12

Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Specifications

Insertion Loss	0.5dB (0.35dB typical), 0.75dB max
Mating durability	500 cycles <
Multimode return loss	35dB Typ, 22dB minimum
Singlemode return loss	55dB Typ, 40dB minimum
Operating temperature	0 °C to +70 °C