

HI-Impact POLYTUFF Non-Metallic Conduit

HUBBELL

Features

- Maximum Protection for Abusive Environments
- Rigid PVC Core Bonded to Flexible PVC Jacket
- All Non-Metallic Construction
- Cuts Cleanly With Knife or PVC Cutter

Ordering Information

Description	Color	Catalog Number	UPC
HI-Impact POLYTUFF Non-Metallic Conduit, 1/2 in., 100 feet	Gray	G1050	783585333632



Listings

UL Listed 1660. Approved for outdoor and direct burial
CSA Certified

Specifications

Material Co-extruded rigid and flexible PVC

Performance

Electrical Voltage Rating: 600V

Environmental Ingress Protection: IP66 (dust/water)

Operating Temperature Range
Wet Environment: 0°F to 140°F (-18°C to 60°C)
Oil Environment: 0°F to 158°F (-18°C to 70°C)
Dry Environment: 0°F to 176°F (-18°C to 80°C)

Accessories

Straight Liquid-Tight Connector	P050NGYA
SwivelLock Liquid-Tight Connector	PS0509NGY

Online Resources

eCatalog