

Features

- Ceiling trim mounting plate and scuff boot included
- All conductors are #12 AWG stranded copper
- Ready for quick installation
- UL Listed

Ordering Information

| Style | Color/Finish | Catalog Number | UPC Number |
|--|-------------------------------|----------------|--------------|
| (1) 20A GFCI Duplex, (2) 20A Ground Fault Protected Duplex | Clear Anodize Aluminum finish | HBLPP10GFAL | 783585483924 |



Listings

UL Listed

Specifications

| | |
|----------|-----------|
| Circuits | 1 Circuit |
|----------|-----------|

Dimensions- inches (mm)

| | |
|--------|--------------|
| Length | 10'2" (3100) |
| Width | 2.13" (54) |
| Depth | 2.1" (54) |

Characteristics

| | |
|--------------------|----------|
| Ceiling Trim plate | Included |
| Divider | Included |
| Scuff Boot | Included |

Accessories

| | |
|--------------------------|---------|
| Adjustable T-bar bracket | ATB |
| Replacement trim kit | PPTRIM1 |

Online Resources

[Delivery Systems Guide](#)
[eCatalog](#)
[Product Drawing](#)
[Service Poles Guide](#)