

NEXTSPEED
Category 6 Patch Cords

HUBBELL

Patch Cord

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level



Ordering Information


| Description | Color | Catalog Number | UPC |
|-----------------------------|-------|----------------|--------------|
| 5 ft. Category 6 Patch Cord | Red | HC6OR05 | 662620232652 |

Listings

ANSI/TIA/EIA-568-C.2 Category 6 component
ISO 11801/60603-7-41 Category 6 component
Mechanical: Verified to TIA-568-C.2
UL Listed 1863

Specifications

| | |
|-----------------|--|
| Conductor | 24AWG UTP |
| Jacket | Flame-Retardant PVC-CM Rated |
| Plug Body | Polycarbonate UL 94V-0 |
| Plug Boot | Polycarbonate UL 94V-0 |
| Contact Plating | 50 micro-inch Gold with 100 micro-inch under plating |
| OD | 0.224 in. |



Performance

Mechanical

| | |
|--------------------------------|----------|
| Cable to plug tensile strength | 20+ lbs. |
| Mating Cycles | 2000+ |

Applications

IEEE 802.3ab 1000GBASE-T
IEEE 802.3bt 4PPoE Power over Ethernet
TIA TSB-155 10GbE Over 55 Meters
Backward compatible with Cat 5E hardware and applications

Accessories

| | |
|--------------------------------|---------------|
| Category 6 Component Jack | HXJ6OR |
| Category 6 24-Port Patch Panel | HP624 |
| Category 6 48-Port Patch Panel | HP5E48 |

Online Resources

Customer Use Drawing
Customer Use Drawing
eCatalog