

## Patch Cord

### Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- 10-Gigabit Application Assurance
- Qualified to 150% of 802.3bt PoE Current Level



### Ordering Information

Description	Color	Catalog Number	UPC
10 ft. Category 6 Patch Cord	Gray	<b>HCL6GY10</b>	

### Listings

ANSI/TIA/EIA-568-C.2 Category 6 component  
UL Listed 1863

### Specifications

Conductor	28AWG UTP
Jacket	Flame-Retardant PVC-CMR Rated
Plug Body	Polycarbonate UL 94V-0
Plug Boot	Polycarbonate UL 94V-0
Contact Plating	50 micro-inch Gold with 100 micro-inch under plating
OD	0.155 in.

### Performance

#### Mechanical

Cable to plug tensile strength	20+ lbs.
Mating Cycles	2000+

### Applications

IEEE 802.3an 10GBASE-T  
IEEE 802.3bt 4PPoE Power over Ethernet

### Accessories

Category 6 Component Jack	<b>HXJ6GY</b>
Category 6 24-Port Patch Panel	<b>HP624</b>
Category 6 48-Port Patch Panel	<b>HP648</b>

### Online Resources

[eCatalog](#)