

Full Size Data Center Cabinet HDC Series Complete Cabinet Solution

HUBBELL

Features

- Supports up to 4,000 lbs static load on robust welded frame construction
- Mesh doors with lockable handle; reversible front and split rear
- Locking split sidewalls
- Top and bottom cable access
- Two pairs of movable EIA mounting rails

Ordering Information

Width and depth (inches)	Rack Spaces	Catalog Number	UPC
24 X 44	48	HDC482444WH	662620367965



Listings

UL 2416
EIA 310-E Universal Mounting Pattern

Specifications

Color	White
Finish	Durable textured powdered coating
Sidewalls	Locking split
Cable access	Full width brush able access on cabinet top front and rear for easy cable routing
PDU mounting	2 brackets included

Performance

Equipment mounting

Supports 19" wide rack mount equipment with included M6 cage nuts

Mesh door

77% airflow

Static Load Capacity

4,000 lbs

Accessories

Snap in cabinet cable management fingers (pack of 6) **HDCVCM**

Front to rear cable management trough in black **HDCFRT**

1 RU cabinet filler panel in black (pack of 10) **HDCFP**

2 RU Cabinet filler panel n black (pack of 5) **HDCFP2**

Online Resources

eCatalog

