

## HFCD15 Series Hubbell Brand Indoor Tight Buffer Distribution

# HUBBELL

### Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber E-Z
- Strip Buffer For Contractor-Friendly Termination
- Durable Aluminum Interlock Armor
- Premium Fiber For Enhanced Optical Performance

### Ordering Information

---

<b>Catalog No.</b> HFCB15012P4	<b>UPC</b> 662620340746
-----------------------------------	----------------------------

### Listings

---

ANSI/ICEA S-83-596  
NFPA-262/UL910/CSA FT-6  
Telcordia GR-409  
TIA-568.3-D

### Specifications

---

Number of Fibers	12
Cable Rating	Plenum, Armored
Fiber Type	OM4, MM
Color	Aqua

### Characteristics

---

Application	Data Transmission
Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Material - Jacket	PVC
Temperature Rating	0 Degrees °C to 70 Degrees °C
Wavelength	850/1300 Nanometers

