

HFCD19 Series Hubbell Brand Indoor/Outdoor Tight Buffer

HUBBELL

Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber E-Z
- Strip Buffer For Contractor-Friendly Termination
- Multi-Purpose Outdoor Duct To Building Riser Application
- Premium Fiber For Enhanced Optical Performance

Ordering Information

Catalog No.	UPC
HFCB19012P4BK	662620340760

Listings

ANSI/ICEA S-83-596
NFPA-262/UL910/CSA FT-6
Telcordia GR-409
TIA-568.3-D

Specifications

Number of Fibers	12
Cable Rating	Plenum, Armored
Fiber Type	OM4, MM
Color	Black

Characteristics

Application	Data Transmission
Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Material - Jacket	PVC
Temperature Rating	0 Degrees °C to 70 Degrees °C
Wavelength	850/1300 Nanometers

