

Plenum

Features

- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Bend-Insensitive Fiber For Enhanced Optical Performance

Ordering Information

Description	Fiber Type	Catalog No.	UPC No.
Indoor Tight Buffer Distribution, 2 Fiber, Plenum, Aqua	OM4 Multimode	HFCD1002P4	662620555461

Listings

ANSI/ICEA S-83-596
TIA-568.3-D
NFPA-262/UL910/CSA FT-6
Telcordia GR-409 and GR-20

Specifications

Fiber Coating	900 Micron PVC Tight Buffer
Cable Diameter in (mm)	0.17 (4.4)
Cable Weight (lb/kft)	12
Construction	Single Unit, Aramid Strength Member
Armor	None

Performance

Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

Maximum Installation Pulling Load (lb)

99

Maximum Operating Temperature

-4°F to +158°F (-20°C to +70°C)

Minimum Bend Radius, In-Service in (cm)

1.7 (4.4)



Accessories

Fiber Strip Tool	OFSTRIP2
Splice Tray, 12 Fusion	STRAY12F
Splice Tray, 24 Fusion	STRAY24F
Splice Protection Sleeves	FSHST401025

Online Resources

[eCatalog](#)