

OptiChannel Indoor Distribution Cable Riser

HUBBELL

Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Ordering Information

Description	Fiber	Catalog Number	UPC Number
12 strand, OM3, MM, Riser, Indoor Tight Buffer Distribution - Aqua	OM3 Multimode	HFCD1012R3	662620327259



Listings

ANSI/CEA S-83-596
TIA-568.3-D
NFPA-262/UL910/CSA FT-6
Telcordia GR-409 and GR-20

Specifications

Fiber Coating	900 Micron PVC Tight Buffer
Cable Diameter in (mm)	0.25 (6.3)
Cable Weight (lb/kft)	35
Construction	Single Unit, Aramid Strength Member
Aarmor	None

Performance

Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

Maximum Installation Pulling Load (lb)

160

Maximum Operating Temperature

-4°F to +158°F (-20°C to +70°C)

Minimum Bend Radius, In-Service in (cm)

2.3 (5.8)

Accessories

Fiber Strip Tool	OFSTRIP2
Splice Tray, 12 Fusion	STRAY12F
Splice Tray, 24 Fusion	STRAY24F
Splice Protection Sleeves	FSHST401025

Online Resources

eCatalog