

OptiChannel Indoor/Outdoor Tight Buffer Cable Plenum

HUBBELL

Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance



Ordering Information

Description	Fiber	Catalog Number	UPC Number
6 strand, OM4, MM, I/O Tight Buffer Plenum, Indoor/Outdoor Tight Buffer - Black	OM4 Multimode	HFCD14006P4BK	662620332192

Listings

ANSI/CEA S-83-596
TIA-568.3-D
NFPA-262/UL910/CSA FT-6
Telcordia GR-409 and GR-20

Specifications

Fiber Coating	900 Micron PVC Tight Buffer
Cable Diameter in (mm)	0.21 (5.3)
Cable Weight (lb/kft)	20
Construction	Single Unit, Aramid Strength Member
Armor	None

Performance

Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

Maximum Installation Pulling Load (lb)

150

Maximum Operating Temperature

-4°F to +185°F (-20°C to +85°C)

Minimum Bend Radius, In-Service in (cm)

2.1 (5.3)

Accessories

Fiber Strip Tool	OFSTRIP2
Splice Tray, 12 Fusion	STRAY12F
Splice Tray, 24 Fusion	STRAY24F
Splice Protection Sleeves	FSHST401025

Online Resources

eCatalog

