

# Grounding & Bonding Conductor Kit, #6 AWG insulated Lug With C-Tap Kit

# HUBBELL

## Features

- Ideal for Bonding Cabinet to Raised Floor or Bonding Conductor
- Includes Anti-Oxidant, Identification Labels and Instructions
- Stainless Steel Hardware

## Ordering Information

| Length | Kit Type        | Catalog Number | UPC          |
|--------|-----------------|----------------|--------------|
| 45"    | Lug & C-Tap Kit | HGRKTD45C46    | 662620326320 |

## Listings

Meets TIA-607

## Specifications

|          |                                    |
|----------|------------------------------------|
| Material | Copper                             |
| Finish   | PVC Coated Green                   |
| Lug Type | Long barrel with inspection window |
| C-Tap    | #6 to #4 or #6 compression         |

## Characteristics

|           |                      |
|-----------|----------------------|
| Lug       | Crimped to Conductor |
| Conductor | Labeled              |

## Accessories

|                                 |                   |
|---------------------------------|-------------------|
| Horizontal rack bonding bus bar | <b>HBBBHR19KT</b> |
| Manual Compression Tool         | <b>HMD7</b>       |
| Black Velcro Roll               | <b>HVFBK575</b>   |
| 9" Velcro Strips, Yellow        | <b>MCCMV9YL10</b> |
| Flat blanking panel, 2U         | <b>MCCBM350</b>   |

## Online Resources

eCatalog



## Dimensions- inches (mm)

|             |            |
|-------------|------------|
| Length      | 45" (1143) |
| Lug hole ID | 1/4" (6)   |