

HI-Impact POLYTUFF Thermoplastic 4-Point FS/FD Plate

HUBBELL

Features

- IP55 Rated for Dust and Liquids
- Pre-Punched, Keyed Opening for HI Connector
- Single and Double Gang Offerings
- Gasketed to Protect from Elements

Ordering Information

Description	Color	Catalog Number	UPC
HI-Impact Thermoplastic 4-Point FS/FD Plate, 1-Port, 1-Gang	Gray	HI14GY	662620850269

Listings

UL Listed

Specifications

Flammability	UL 94V0, 94-5VA classification
Material	Thermoplastic with closed-cell foam gasket
Mounting Screws	Stainless Steel
Dimensions	4.5"H (114.3) x 2.78"W (70.6)

Performance

Environmental	Operating Temperature: TIA/EIA 568-B.2 -25°C
	UV Resistance: All materials are UV stabilized

Accessories

High-Impact Category 5E Connector	HI5E
High-Impact Category 5E Coupler	HI5EC
High-Impact Category 6 Connector	HI6
High-Impact Category 6 Coupler	HI6C
High-Impact Protective Cap	HIC

Online Resources

eCatalog

