

HI-Impact Plates Stainless Steel Plate

HUBBELL

Features

- IP55 Rated for Dust and Liquids
- Pre-Punched, Keyed Opening for HI Connector
- Constructed From 302/304 Stainless Steel
- Gasketed to Protect from Elements

Ordering Information

Description	Color	Catalog Number	UPC
HI-Impact Stainless Steel Plate, 2-Port, 1-Gang	Stainless Steel	HISF12	662620846736

Listings

UL Listed



Specifications

Thickness	.04" (.9) nominal
Material	Smooth metal 302/304; super stainless steel 17-19%; chrome, 8% nickel
Mounting Screws	302/304 stainless steel (18% chromium, 8% nickel)
Appearance	Smooth brushed finish
Gasket Material	Closed-cell foam
Dimensions	4.5"H (114.3) x 2.78"W

Applications

Industrial, institutional, pharmaceutical, hospital and harsh commercial applications

Accessories

High-Impact Category 5E Connector	HI5E
High-Impact Category 5E Coupler	HI5EC
High-Impact Category 6 Connector	HI6
High-Impact Category 6 Coupler	HI6C
High-Impact Protective Cap	HIC

Online Resources

eCatalog