

# HI-Impact Plates Stainless Steel Plate

# HUBBELL

## Features

- IP55 Rated for Dust and Liquids
- Pre-Punched, Keyed Opening for HI Connector
- Constructed From 302/304 Stainless Steel
- Gasketed to Protect from Elements

## Ordering Information

Description	Color	Catalog Number	UPC
HI-Impact Stainless Steel Plate, 2-Port, 2-Gang	Stainless Steel	HISF22	662620846743

## Listings

UL Listed

## Specifications

Thickness	.04" (.9) nominal
Material	Smooth metal 302/304; super stainless steel 17-19%; chrome, 8% nickel
Mounting Screws	302/304 stainless steel (18% chromium, 8% nickel)
Appearance	Smooth brushed finish
Gasket Material	Closed-cell foam
Dimensions	4.5"H (114.3) x 4.60"W

## Applications

Industrial, institutional, pharmaceutical, hospital and harsh commercial applications

## Accessories

High-Impact Category 5E Connector	<b>HI5E</b>
High-Impact Category 5E Coupler	<b>HI5EC</b>
High-Impact Category 6 Connector	<b>HI6</b>
High-Impact Category 6 Coupler	<b>HI6C</b>
High-Impact Protective Cap	<b>HIC</b>

## Online Resources

eCatalog

