HI-Impact

Plates

Stainless Steel Plate

HUBBELL

Features

- · IP55 Rated for Dust and Liquids
- · Pre-Punched, Keyed Opening for HI Connector
- Constructed From 302/304 Stainless Steel
- · Gasketed to Protect from Elements

Ordering Information

DescriptionColorCatalog Number UPCHI-Impact Stainless SteelStainless SteelHISF24662620846750Plate, 2-Port, 1-Gang

Listings

UL Listed

Specifications

Thickness .04" (.9) nominal

Material Smooth metal 302/304; super stainless steel 17-19%; chrome, 8% nickel

Mounting Screws 302/304 stainless steel (18% chromium, 8% nickel)

Appearance Smooth brushed finish

Gasket Material Closed-cell foam

Dimensions 4.5"H (114.3) x 4.60"W

Applications

Industrial, institutional, pharmaceutical, hospital and harsh commercial applications

Accessories

High-Impact Category 5E Connector
High-Impact Category 5E Coupler
High-Impact Category 6 Connector
High-Impact Category 6 Coupler
High-Impact Category 6 Coupler
High-Impact Protective Cap
HIC

Online Resources

eCatalog



