# **NEXTSPEED® Jacks**

# HUBBELL

# **Ascent Category 6A Jack**

#### **Features**

- Third Party Verified Category 6A Component Exceeds TIA and ISO
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- Qualified to 150% of 802.3bt PoE Current Level
- Bulk and Green Packaging Reduces Excess Waste on the Job **Ordering Information**

Description	Color	Catalog No.	UPC
NEXTSPEED Ascent	Yellow	HJ6AY	662620214030
Category 6A Component			
lack 1 lack			

# Listings

ANSI/TIA/EIA-568-C.2 Category 6A component ISO 11801/60603-7-41 Category 6A component Mechanical: Verified to TIA-568-C.2 UL Listed 1863 Mechanical TIA-568-C.2 RoHS Compliant

# **Specifications**

Nose Contact	Beryllium copper with precious metal plating with nickel under-plating	
IDC Contact	Phosphor bronze with 100 micro-inch tin lead 60/40 plating over nickel under plating	
Housing	High impact thermoplastic (UL 94 V-0)	
Packaging	Carton 100% recycled material - bag 85% recycled material	

# **Performance**

#### **Electrical**

4.5db min NEXT margin over TIA 568-C.2 component at 500MHz 1.5 dB min NEXT margin over ISO component Qualified to 150% of 802.3bt PoE Current Level Enhanced common mode design eliminates residual and reflected NEXT and

# **General Information**

Backward compatible to Category 6, & 5e Icon Compatible Supporting 606-B requirements HJ6Axx Jacks are not compatible with RJ11, RJ14 or RJ25 6-position plugs 100% factory tested

#### Mechanical


Nose Contact Mating Cycles: 2000 IDC Contact Termination: 10x Keystone Latching Force: 25 lbs.


Contact performance confirmed over the full range of ISO/FCC compliant plug


### **Applications**

IEEE 802.3an 10GBASE-T IEEE 802.3bt 4PPoE Power over Ethernet IEEE 802.11ac and IEEE 802.11ax WAP Deployments









#### **Accessories**

1-Punch Tool	TX4P6A
Category 6A Patch Cord	HC6AY03
Dust Cover	HXJDC25
Ascent Termination Puck	HJTP6A25
Category 6A Cable	C6ASPB

# Online Resources

eCatalog

