

NEXTSPEED®

# Jack Category 6A Jack with Cobra-Lock™ Termination

# HUBBELL

- Third Party Verified Category 6A Component
- Cobra-Lock™ Termination Reduces Termination Time by Over 75%
- Wires Secured Under Constant Compression
- Easily Re-Terminate
- Qualified to 150% of 802.3bt PoE Current Level

## Ordering Information

Description	Qty	Color	UPC Number	Catalog Number
NEXTSPEED Ascent Category 6A Jack with Cobra-Lock Termination	24	Green	662620663425	HJU6AGN24

## Listings

ANSI/TIA/EIA-568 Category 6A component  
UL 1863 - Communications-Circuit Accessory  
UL 2043 - Suitable for Air-Handling Spaces  
RoHS Compliant  
IEC60512-99-002 for de-matting endurance under PoE load

## Specifications


Nose Housing Material	High-impact thermoplastic (UL 94V-0)
Rear Housing Material	Zinc die-cast
Nose Contacts	Copper Alloy with Gold Over Plating
IDC Contacts	Phosphor bronze with 100 micro-inch tin over plating
Dimensions in (mm) (H x W x D)	0.87 (22) x 0.67 ( 17) x 1.39 ( 35)
Wire Compatibility	24-22 AWG Solid

## Performance

Electrical Performance	TIA Component Compliant
Withstand Voltage	1,000 Vac @ 60 Hz
PoE Support	Qualified to 150% of 802.3bt PoE Current Level
Plug Mating Cycles	750 Minimum
IDC Re-termination Cycles	25 Maximum
Plug Compatibility	RJ-11 to 45
Testing	100% Factory Tested
Backward Compatibility	Cat5e and Cat6

## Accessories

Description	Catalog Number
Riser Reduced Diameter C6A Cable	C6ASRDSGN
Plenum Reduced Diameter C6A Cable	C6ASPDSGN
Standard C6A Patch Cord	HC6AGN10
Slim 28 AWG C6A Patch Cord	HCL6AGN10
RJ-45 Security Port Blocker, 25 pack	HXJDC25



## Resources

[Customer Drawings](#)  
[eCatalog page](#)