NEXTSPEED®

Jack

Category 6 Jack with Cobra-Lock™ Termination



Features

- Third Party Verified Category 6 Component
- Cobra-Lock™ Termination Reduces Termination Time by Over 75%
- Wires Secured Under Constant Compression
- Easily Re-Terminate
- Qualified to 150% of 802.3bt PoE Current Level

Ordering Information

			UPC	Catalog
Description	Qty	Color	Number	Number
NEXTSPEED Category 6 Jack	1	Green	662620669540	HJU6GN
with Cobra-Lock Termination				

Listings

ANSI/TIA/EIA-568 Category 6 component

UL 1863 - Communications-Circuit Accessory

UL 2043 - Suitable for Air-Handling Spaces

RoHS Compliant

IEC60512-99-002 PoE Disconnection Endruance

Specifications

Nose Housing Material	High-impact thermoplastic (UL 94V-0)	
Rear Housing Material	High-impact thermoplastic (UL 94V-0)	
Nose Contacts	Copper Alloy with Gold Over Plating	
IDC Contacts	Phosphor bronze with 100 micro-inch tin over plating	
Dimensions in (mm) (H x W x D	0.87 (22) x 0.67 (17) x 1.39 (35)	
Wire Compatibility	24-22 AWG Solid	
Performance		
Electrical Performance	TIA Component Compliant	
Withstand Voltage	1,000 Vac @ 60 Hz	
PoE Support	3rd Party Tested to IEC60512-99-002 for PoE disconnection endurance	
Plug Mating Cycles	750 Minimum	
IDC Re-termination Cycles	25 Maximum	
Plug Compatibility	RJ-11 to 45	
Testing	100% Factory Tested	
Backward Compatibility	Cat5e	

