

Wall Mount Cabinets

HLQ Series, General Use Center Swing

Wall Mount Cabinet

HUBBELL

Features

- Locking Front Door and Center Section
- Two pairs of adjustable threaded rails
- U-Knockouts for installing punched down patch panels without disconnecting
- All sections bonded together



Ordering Information

Description	Depth	UPC Number	Catalog Number
Rack 12 Units	24"	662620617718	HLQ24

Listings

EIA/ECA-310-E Universal Mounting Pattern

Specifications

Enclosure Shell Material	16 gauge C.R. Steel
Mounting Rails	12 gauge C.R. Steel
Material Finish	Black Powder Coat
Rail Type	#12-24 Threaded

Performance

Load Capacity	150 lb
Rack Units	12
Front Door	Window
Mounting	Slotted holes to align with 16" spaced studs

Accessories

Horizontal rack bonding bus bar	HBBBHR19KT
Fan Kit	HLQFK
1U Horizontal cable manager	HS13C
8" Velcro Straps	HPWCVFBK8

Resources

Customer Drawing
Brochure
HEQ Sheet

