

Power and AV Enclosures
AV In-Wall and Ceiling Enclosures
Power and AV Wall Enclosures

HUBBELL

Features

- 16 gauge steel back box with black two piece cover
- 2" conduit feed-through with 1" and 1-1/2" concentric knockouts
- Four old work box knockouts for top or bottom feed
- 2" x 4" x 16" on-center flush mounting
- Can also be used as in-wall storage box

Ordering Information

Description	Color	Catalog Number	UPC
Recessed Wallbox, 5-Gang, 2" Conduit feed-Thru, Black	Black	HRWB25BLK	783585695792



Listings

ETL Listed
Conforms to UL 62368-1:2019 Ed.3
Certified to CSA C22.2#62368-1:2019 Ed.3

Specifications

Box Material	16 Gauge Pregalvanized Steel
Cover Material	Steel
Cover Finish	Black paint
Box Dimensions in (mm) (H x W x D)	7.24" (183.8) x 14.25" (362.0) x 4.00" (141.6)
Cover Dimensions in (mm) (H x W x D)	8.34" (211.7) x 15.50" (393.7) x 0.16" (4.0)
Cover Paintable	Yes

Performance

Accessories

3/4" masonry, steel and wood frame box extension	HRWB25BE075
Surge Protected Power Kit	NSOKPS
Power Kit	NSOKPTR
1-Gang, 6-Port Multimedia Face Plate, Gray	IFP16GY
1-Gang, 6-Port Multimedia Face Plate, White	IFP16W

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions