

Mounted Zone Cabling Enclosures and Brackets
 Wall Mounted Enclosure
 QuadCab Enclosure, 20" depth

HUBBELL

Features

- Modular construction with mid-section to swing out to access rear installed equipment
- Modular backboard systems eliminates field engineering
- Distributing network equipment lessens heat load in the telecom room

Ordering Information

Height	Door Style	Catalog Number	UPC Number
24"	Solid Door	HSQ24S	662620853208

Listings

EIA/ECA-310-E Universal Mounting Pattern

Specifications


Material	Cold rolled steel
Rear & Middle Gauge	14
Door Gauge	18
Door Type	Solid
Rail Type	#12-24 Threaded
Finish	Black powder coat

Characteristics

Access	Swing out center section
Load Capacity	403 lb
Rack Units	12

Accessories

1U Power strip	HPWPWR
1U Horizontal cable manager with cover	HM14C
2U Horizontal cable manager with cover	HM24C
Mobile Base	HSQKMB20



Dimensions- inches (mm)

A	24.1" (612)
B	22.6" (574)
C	20.3" (516)

Online Resources

[Customer Drawing](#)
[Customer Use Drawing](#)
[eCatalog](#)