

Xcelerator Category 5e Jack



- Third Party Verified Category 5e Component Compliant
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- Mating Cycles Exceed Industry Standard by Four Times
- Bulk Packaging Reduces Excess Waste on the Job

Features

- IDC towers have an inner blade to assist in pair splitting without performance disruption.
- Small form factor allows more jacks in devices without restriction or constraint.
- Two distinct labels eliminate wiring confusion, T568B or T568A.

Ordering Information

Description Cat 5e Keystone RJ45 Jack, 110 Termination	Color	UPC #	Catalog No.
	Telco Ivory	662620825175	HXJ5ETI25
Jack, 110 Terrimation			

Listings

ANSI/TIA/EIA-568-C.2 category 5e component ISO 11801 class D compliant IEE 802.3 Gigabit Ethernet Transmission IEE 802.3at PoE+ Power over Ethernet Mechanical TIA-568-C.2 UL Listed 1863 CSA Certified

Specifications

Nose Contact	Beryllium copper with precious metal plating with nickel under-plating
IDC Contact	Phosphor bronze with 100 micro-inch tin lead 60/40 plating over nickel under plating
Housing	High impact thermoplastic (UL 94 V-0)

Performance

Application

10/100/1000BASE-T

Electrical

Exceeds component requirements by a minimum of 3dB

Positive PSACR beyond 190 MHz (channel)

Center balanced to Category 5e plug specifications

Designed and tested for 850mA of continuous current per conductor (1.7A per pair).

General Information

Icon Compatible Supporting 606-B requirements
Backward Compatible to lower installed Categories

100% factory tested.

Mechanical


Contact performance confirmed over the full range of ISO/FCC compliant plug dimensions

Nose contact mating cycles RJ45: 2000

IDC contact termination: 10X Keystone latching force: 25 lbs.







Accessories

Ascent termination puck	HXTP25
1-punch tool	TX4P
Dust Cover	HXJDC25

Resources

Customer Drawings eCatalog Specification Text Division 17

