# Xcelerator Jacks

# HUBBELL

# **Xcelerator USOC Jack**

#### **Features**

- RJ-25 USOC (RJ-25) Jack
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- · Mating Cycles Exceed Industry Standard by Four Times
- · Bulk Packaging Reduces Excess Waste on the Job

## **Ordering Information**

Description	Color	Catalog No.	UPC
Xcelerator USOC Jack	Red	HXJUR	662620824819



6-Position USOC Compliant Mechanical TIA-568-C.2 UL Listed 1863 CSA Certified RoHS Compliant

## **Specifications**

Nose Contact	Beryllium copper with precious metal plating over nickel under plating
IDC Contact	Phosphor bronze with 100 micro-inch tin lead 60/40 plating over nickel under plating
Housing	High impact thermoplastic (UL 94 V-0)

#### **Performance**

#### **Electrical**

6-Position USOC Compliant

#### Mechanical

Nose Contact Mating Cycles: 2000 IDC Contact Termination: 10x Keystone Latching Force: 25 lbs.

Contact performance confirmed over the full range of ISO/FCC compliant plug

## **Applications**

Phone DSL

# Accessories

1-Punch Tool	TX4P
Dust Cover	HXJDC25
Termination Puck	HXTP25

#### **Online Resources**

eCatalog



