

Mounted Zone Cabling Enclosures and Brackets

Wall Mounted Enclosure

IDF User Configurable ReBox

HUBBELL

Features

- Concentric knockouts for conduit and retangular metal or PVC raceway
- Door lifts off when open for easy installation of cabling and equipment
- Flexible mounting solutions for active equipment and UPS

Ordering Information

Height	Finish	Catalog Number	UPC Number
42"	Light Gray	IDF42	662620827995

Listings

UL Listed

Specifications

Material	Cold rolled steel
Gauge	16
Finish	Light Gray
Rail Type	#12-24 Threaded
Rack Units	5
NEMA Rating	2

Characteristics

Load Capacity	100 lb
Rack Units	User Configured with Accessories

Accessories


5U Bracket	REKZ
1U Power strip	HPWPWR
Black Velcro Roll	HVFBK575
9" Velco Strips, Yellow	MCCMV9YL10
#12-24 Screws	1224RRSCRW20

Online Resources

Customer Drawing

Customer Use Drawing

eCatalog



Dimensions- inches (mm)

A	42" (1067)
B	24.2" (615)
C	9.7" (246)