

Mounted Zone Cabling Enclosures and Brackets

Industrial ReBox Enclosure with Slide-Out Equipment Mounting Rails

NEMA 4/12 ReBox Enclosure

HUBBELL

Features

- Equipment mounted on slide out rails allows for rear access
- Side opening doors allow easy mounting of cable to rear panel
- Continuous plasma-welded seams provide a seal to protect equipment from water intrusion

Ordering Information

NEMA Rating	Finish	Catalog Number	UPC Number
4 / 12	Gray powder coated	IR423PG3	662620661285



Listings

NEMA Rated 4 / 12
EIA/ECA-310-E Universal Mounting Pattern
UL Listed

Specifications

Material	Carbon Steel
Gauge	14
Finish	Light Gray
NEMA Rating	4 / 12
Rail Type	#12-24 Threaded
Rack Units	26

Dimensions- inches (mm)

A	48" (1219)
B	24" (610)
C	30" (762)

Accessories

Screw Mount Velco	MCCMV9BS10
Heater Thermostat	CTKH
250W Heater	IRH250
#12-24 Screws	1224RRSCRW20

Online Resources

eCatalog
Product Guide