

Istation
A/V
HDBaseT Extender



Features

- Locate a display device up to 328 feet (100m) away
- Terminate with one Category 6a UTP or Shielded Cable
- 110 Punchdown Termination Reduces Installation Time
- Source & Display Module can both be installed in back boxes

Ordering Information

Description	Color	Catalog Number	UPC
110 HDBaseT Extender,4K HDMI, USB, 3.5mm Audio, IR, 1 Gang Decorator, Black, Tx & Rx Module	Black	ISFHD5BK	662620343228

Listings

Listed UL AZOT/7

Specifications

Material	Steel Housing & Mounting Strap, Thermoplastic Face
IDC Contact	Phosphor bronze with tin plating over nickel under plating
HDMI Connector	HDMI 19-pin, Type A, female connector, gold plated 2μ"
Audio Signal	Audio signal: 2ch PCM; up to 7.1 DTS-X and DOLBY ATMOS®
Type A, 2.0 High Speed (480mbps), selectable Host or Device	USB
Audio	Analog audio pass through 3.5mm jacks
Cabling	Category 6A or higher cables required; up to 328 ft (100m)
Power	Front or rear 5V DC input on each device
DC power wire length	Up to 50ft with 16 AWG

Performance

Color
4:4:4 24bit
HDMI
18Gbps - 4K@60Hz 4:4:4 (100m/328ft)
HDMI Features
HDCP 2.2, CEC Control
Video maximum support
4K: 4096 x 2160 or 3840 x 2160p @ 60Hz



Accessories

AV Power Supply Receptacle	AVPS152W
5V DC External Power Supply	HDMIDC5V2
Two Gang AV Back Box	HBL985
HDMI Patch Cable, High Speed, Black, 3 ft	HCH03BK
HDMI Patch Cable, High Speed, Black, 6 ft	HCH06BK

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

