

## Patch Cord

### Features

- Category 6 Performance
- Slim Snagless Boot or High Density Ports
- PoE Ready



### Ordering Information

Description	Color	Catalog Number	UPC
10 ft. Category 6 Patch Cord	Gray	NSC6GY10	883778505096

### Listings

ANSI/TIA/EIA-568-C.2 Category 6 channel  
Mechanical: Verified to TIA-568-C.2

### Specifications

Conductor	24AWG UTP
Jacket	Flame-Retardant PVC-CM Rated
Plug Body	Polycarbonate UL 94V-0
Plug Boot	PVC
Contact Plating	50 micro-inch Gold

### Performance

#### Mechanical

Cable to plug tensile strength	20+ lbs.
Mating Cycles	2000+

### Applications

IEEE 802.3ab 1000GBASE-T  
Backward compatible with Cat 5E hardware and applications

### Accessories

netSELECT Category 6 Jack	NSJ6GY
netSELECT Unloaded 24-Port Panel	NSPJ24
netSELECT Unloaded 48-Port Patch Panel	NSPJ48

### Online Resources

eCatalog